


The information and specifications included in this publication were in effect at the time of approval for printing. Illustrations, descriptions, references and technical data contained in this document are for guidance only and may not be considered as binding. Multiquip Inc. reserves the right to discontinue or change specifications, design or the information published in this publication at any time without notice and without incurring any obligations.

CORRECT RECEPTACLE AND EXTENSION CORD SIZING

This trowel is equipped with a 1 Ø, 60 Hz, 2 HP motor. The motor is factory configured for 230V operation. Make certain that the correct Receptacle “Ref. Fig. 1” is used (**L6-20R**) on a correctly sized, grounded, 3-wire type extension cord and if applicable that it’s plugged into a properly sized portable generator “Ref. Fig. 2” table below.



© COPYRIGHT 2020, MULTIQUIP INC, Rev. 0 (04132020)